



Hexagon flange bolt, fully threaded DIN ≈6921 Stainless steel A2 70 M5X25

Article number	51018.050.025
Brand	-
UBB	500635892747
UNSPSC	31161620
EAN	8715494551014
PKG. of 200	Full Box Only

Technical Parameters

Diameter (d-D)	M5
Length (L) (mm)	25
Class	70
Driving features	Hexagon
Head shape	Hexagon head
Material	Stainless steel
Material technical	A2
Thread direction	Right
Thread	Metric thread

Standards

ASME	≈B18.2.3.4M
ISO	≈4162
DIN	≈6921
EN	≈1665

Technical Specification

b (min.)	16
d _c (max.)	11.8
k (max.)	5.4
P	0.80
s	8

Technical Drawing

