



**Hexagon socket button head screw with flange ISO 7380-2  
Stainless steel A2 M5X45**

Article number	51028.050.045
Brand	-
UBB	500633126106
UNSPSC	31161518
EAN	8715494606769
PKG. of 200	Full Box Only

**Technical Parameters**

Diameter	M5
Length	45 mm
Driving features	Hexagon socket
Head shape	Button head
Material	Stainless steel
Material technical	A2
Thread direction	Right
Thread	Metric thread

Info	Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class mark, e.g. 'A2-070', or with the steel grade only, e.g. 'A2'.
------	--

**Standards**

ISO	7380-2
-----	--------

Technical Specification

d-D	M5
dc (max.)	11.8
Full thread if $L \leq$	25
k (max.)	2.75
L (mm)	45
P	0.8
s	3

Technical Drawing

