



Hexalobular socket button head screw ISO ≈7380-1 Stainless steel A2 M3X3

Article number	51029.030.003
Brand	-
UBB	500635830127
UNSPSC	31161518
EAN	8715494552226
PKG. of 1000	Full Box Only

Technical Parameters

Diameter	M3
Length	3 mm
Driving features	Hexalobular
Head shape	Button head
Material	Stainless steel
Material technical	A2
Thread direction	Right
Thread	Metric thread

Standards

ASME	≈B18.3.4M
ISO	≈7380-1
NF	≈E25-126
BS	≈4168-6

Info	Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class mark, e.g. 'A2-070', or with the steel grade only, e.g. 'A2'.
------	----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

Technical Specification

d-D	M3
dk (max.)	5.7
k (max.)	1.65
L (mm)	3
P	0.5
Socket	10

Technical Drawing

