



**Hexagon socket button head screw ISO 7380-1 Stainless steel A2 M6X120**

Article number	51030.060.120
Brand	-
UBB	500633135198
UNSPSC	31161518
EAN	8715494607674
PKG. of 100	Full Box Only

**Technical Parameters**

Diameter	M6
Length	120 mm
Driving features	Hexagon socket
Head shape	Button head
Material	Stainless steel
Material technical	A2
Thread direction	Right
Thread	Metric thread

Info

Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class mark, e.g. 'A2-070', or with the steel grade only, e.g. 'A2'.

**Standards**

ASME	≈B18.3.4M
BS	≈4168-6
NF	≈E25-126
ISO	7380-1

Technical Specification

d-D	M6
dk (max.)	10.5
Full thread if $L \leq$	30
k (max.)	3.3
L (mm)	120
P	1
s	4

Technical Drawing

