



## Hexagon socket button head screw ISO 7380-1 Stainless steel A2 M8X14

Article number	51030.080.014
Brand	-
UBB	500633135271
UNSPSC	31161518
EAN	8715494607681
PKG. of 100	Full Box Only

### Technical Parameters

Diameter	M8
Length	14 mm
Driving features	Hexagon socket
Head shape	Button head
Material	Stainless steel
Material technical	A2
Thread direction	Right
Thread	Metric thread

### Standards

ASME	≈B18.3.4M
ISO	7380-1
BS	≈4168-6
NF	≈E25-126

**Info**

Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class mark, e.g. 'A2-070', or with the steel grade only, e.g. 'A2'.

### Technical Specification

d-D	M8
dk (max.)	14
Full thread if $L \leq$	35
k (max.)	4.4
L (mm)	14
P	1.25
s	5

### Technical Drawing

