



## Hexagon socket button head screw ISO 7380-1 Stainless steel A2 M12X65

Article number	51030.120.065
Brand	-
UBB	500633137335
UNSPSC	31161518
EAN	8715494607902
PKG. of 50	Full Box Only

### Technical Parameters

Diameter	M12
Length	65 mm
Driving features	Hexagon socket
Head shape	Button head
Material	Stainless steel
Material technical	A2
Thread direction	Right
Thread	Metric thread

### Standards

ISO	7380-1
NF	≈E25-126
BS	≈4168-6
ASME	≈B18.3.4M

Info	Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class mark, e.g. 'A2-070', or with the steel grade only, e.g. 'A2'.
------	--

### Technical Specification

d-D	M12
dk (max.)	21
Full thread if $L \leq$	50
k (max.)	6.6
L (mm)	65
P	1.75
s	8

### Technical Drawing

