



## Hexagon socket button head screw ISO 7380-1 Stainless steel A2 M12X100

Article number	51030.120.100
Brand	-
UBB	500633137749
UNSPSC	31161518
EAN	8715494607940
PKG. of 50	Full Box Only

### Technical Parameters

Diameter	M12
Length	100 mm
Driving features	Hexagon socket
Head shape	Button head
Material	Stainless steel
Material technical	A2
Thread direction	Right
Thread	Metric thread

### Standards

BS	≈4168-6
ASME	≈B18.3.4M
ISO	7380-1
NF	≈E25-126

Info	Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class mark, e.g. 'A2-070', or with the steel grade only, e.g. 'A2'.
------	--

### Technical Specification

d-D	M12
dk (max.)	21
Full thread if $L \leq$	50
k (max.)	6.6
L (mm)	100
P	1.75
s	8

### Technical Drawing

