



Hexagon socket head cap screw with low head DIN 7984 Stainless steel A2 M6X22

| | |
|----------------|---------------|
| Article number | 51040.060.022 |
| Brand | - |
| UBB | 500633145585 |
| UNSPSC | 31161605 |
| EAN | 8715494608725 |
| PKG. of 200 | Full Box Only |

Technical Parameters

| | |
|--------------------|----------------------|
| Diameter | M6 |
| Length | 22 mm |
| Driving features | Hexagon socket |
| Head shape | Low cylindrical head |
| Material | Stainless steel |
| Material technical | A2 |
| Thread direction | Right |
| Thread | Metric thread |

| | |
|------|--|
| Info | Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class mark, e.g. 'A2-070', or with the steel grade only, e.g. 'A2'. |
|------|--|

Standards

| | |
|-----|------|
| DIN | 7984 |
|-----|------|

Technical Specification

| | |
|-------------------------|----|
| b (min.) | 18 |
| d-D | M6 |
| dk | 10 |
| Full thread if $L \leq$ | 25 |
| k | 4 |
| L (mm) | 22 |
| P | 1 |
| s | 4 |

Technical Drawing

