



## Hexagon socket head cap screw with low head DIN 7984 Stainless steel A2 M10X90

Article number	51040.100.090
Brand	-
UBB	500633147490
UNSPSC	31161605
EAN	8715494608916
PKG. of 50	Full Box Only

### Technical Parameters

Diameter	M10
Length	90 mm
Driving features	Hexagon socket
Head shape	Low cylindrical head
Material	Stainless steel
Material technical	A2
Thread direction	Right
Thread	Metric thread

Info	Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class mark, e.g. 'A2-070', or with the steel grade only, e.g. 'A2'.
------	--

### Standards

DIN	7984
-----	------

Technical Specification

b (min.)	26
d-D	M10
dk	16
Full thread if $L \leq$	35
k	6
L (mm)	90
P	1.5
s	7

Technical Drawing

