

Hexagon socket head cap screw with low head DIN 7984 Stainless steel A2 M12X65



Article number	51040.120.065
Brand	-
UBB	500633147722
UNSPSC	31161605
EAN	8715494608947
PKG. of 50	Full Box Only

Technical Parameters

Diameter (d-D)	M12
Length (L) (mm)	65
Material	Stainless steel
Head shape	Low cylindrical head
Driving features	Hexagon socket
Thread direction	Right
Thread	Metric thread
Material technical	A2

Standards

DIN	7984
-----	------

Info

Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class mark, e.g. 'A2-070', or with the steel grade only, e.g. 'A2'.

Technical Specification

b (min.)	30
d_k	18
Full thread if $L \leq$	45
k	7
P	1.75
s	8

Technical Drawing

