



Hexagon socket head cap screw with low head and pilot recess DIN 6912 Stainless steel A2 M16X65

Article number	51042.160.065
Brand	-
UBB	500633156137
UNSPSC	31161605
EAN	8715494609784
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M16
Length	65 mm
Driving features	Hexagon socket
Head shape	Low cylindrical head
Material	Stainless steel
Material technical	A2
Thread direction	Right
Thread	Metric thread

Info	Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class mark, e.g. 'A2-070', or with the steel grade only, e.g. 'A2'.
------	--

Standards

DIN	6912
-----	------

Technical Specification

b (min.): 125mmL≤200mm	44
b (min.): L200mm	57
b (min.): L≤125mm	38
d-D	M16
dh	8
dk	24
Full thread if L ≤	50
k	10
L (mm)	65
P	2
s	14

Technical Drawing

