



## Hexagon socket head cap screw with low head and pilot recess DIN 6912 Stainless steel A2 M16X65

|                |               |
|----------------|---------------|
| Article number | 51042.160.065 |
| Brand          | -             |
| UBB            | 500633156137  |
| UNSPSC         | 31161605      |
| EAN            | 8715494609784 |
| PKG. of 25     | Full Box Only |

### Technical Parameters

|                    |                      |
|--------------------|----------------------|
| Diameter (d-D)     | M16                  |
| Length (L) (mm)    | 65                   |
| Material           | Stainless steel      |
| Head shape         | Low cylindrical head |
| Driving features   | Hexagon socket       |
| Thread direction   | Right                |
| Thread             | Metric thread        |
| Material technical | A2                   |

### Standards

|     |      |
|-----|------|
| DIN | 6912 |
|-----|------|

**Info**

Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class mark, e.g. 'A2-070', or with the steel grade only, e.g. 'A2'.

## Technical Specification

|                                |    |
|--------------------------------|----|
| b (min.):<br>125mm < L ≤ 200mm | 44 |
| b (min.): L > 200mm            | 57 |
| b (min.): L ≤ 125mm            | 38 |
| d <sub>h</sub>                 | 8  |
| d <sub>k</sub>                 | 24 |
| Full thread if L ≤             | 50 |
| k                              | 10 |
| P                              | 2  |
| s                              | 14 |

## Technical Drawing

