

## Hexagon socket head cap screw DIN 912 Stainless steel A2 70 M1,6X5



|                |               |
|----------------|---------------|
| Article number | 51050.016.005 |
| Brand          | -             |
| UBB            | 500633156707  |
| UNSPSC         | 31161605      |
| EAN            | 8715494609845 |
| PKG. of 500    | Full Box Only |

### Technical Parameters

|                    |  |
|--------------------|--|
| Diameter (d-D)     | M1,6   |
| Length (L) (mm)    | 5  |
| Class              | 70   |
| Material           | Stainless steel  |
| Head shape         | Cylindrical head   |
| Driving features   | Hexagon socket   |
| Thread direction   | Right  |
| Thread             | Metric thread  |
| Material technical | A2   |
| Info               | Sizes with a diameter M20 are minimal property class 50. |

### Standards

|      |          |
|------|----------|
| ISO  | 4762     |
| BS   | 4168-1   |
| NF   | E25-125  |
| ASME | B18.3.1M |
| DIN  | 912      |

### Technical Specification

|                         |      |
|-------------------------|------|
| b                       | 15   |
| $d_k$ (max.)            | 3    |
| Full thread if $L \leq$ | 16   |
| k (max.)                | 1.6  |
| P                       | 0.35 |
| s                       | 1.5  |

### Technical Drawing

