



Hexagon socket head cap screw DIN 912 Stainless steel A2 70 M1,6X18

Article number	51050.016.018
Brand	-
UBB	500633157200
UNSPSC	31161605
EAN	8715494609890
PKG. of 1000	Full Box Only

Technical Parameters

Diameter	M1.6
Length	18 mm
Class	70
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Stainless steel
Material technical	A2
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 are minimal property class 50.

Standards

NF	E25-125
NEN	1241
ISO	4762
BS	4168-1
DIN	912
ASME	B18.3.1M

Technical Specification

b	15
d-D	M1.6
dk (max.)	3
Full thread if $L \leq$	16
k (max.)	1.6
L (mm)	18
P	0.35
s	1.5

Technical Drawing

