



Hexagon socket head cap screw DIN 912 Stainless steel A2 70 M30X75

Article number	51050.300.075
Brand	-
UBB	500633169346
UNSPSC	31161605
EAN	8715494611138
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M30
Length	75 mm
Class	70
Driving features	Hexagon socket
Head shape	Cylindrical head
Material	Stainless steel
Material technical	A2
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M20 are minimal property class 50.

Standards

NF	E25-125
ASME	B18.3.1M
NEN	1241
DIN	912
ISO	4762
BS	4168-1

Technical Specification

b	72
d-D	M30
dk (max.)	45
Full thread if L ≤	100
k (max.)	30
L (mm)	75
P	3.5
s	22

Technical Drawing

