

Hexalobular socket head cap screw ISO 14579 Stainless steel A2 70 M2X10



Article number	51052.020.010
Brand	-
UBB	500634396450
UNSPSC	31161605
EAN	8715494557856
PKG. of 500	Full Box Only

Technical Parameters

Diameter (d-D)	M2
Length (L) (mm)	10
Class	70
Material	Stainless steel
Head shape	Cylindrical head
Driving features	Hexalobular
Thread direction	Right
Thread	Metric thread
Material technical	A2

Standards

ISO	14579
-----	-------

Technical Specification

b	16
d_k (max.)	3.8
Full thread if $L \leq$	16
k (max.)	2
P	0.40
Socket	T6

Technical Drawing

