



Hexalobular socket head cap screw ISO 14579 Stainless steel A2 70 M4X40

Article number	51052.040.040
Brand	-
UBB	500634400641
UNSPSC	31161605
EAN	8715494559195
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M4
Length	40 mm
Class	70
Driving features	Hexalobular
Head shape	Cylindrical head
Material	Stainless steel
Material technical	A2
Thread direction	Right
Thread	Metric thread

Standards

ISO	14579
-----	-------

Technical Specification

b	20
d-D	M4
dk (max.)	7
Full thread if $L \leq$	25
k (max.)	4
L (mm)	40
P	0.7
Socket	20

Technical Drawing

