



**Hexagon socket  
countersunk head screw  
ISO 10642 Stainless steel A2  
M8X100**

Article number	51060.080.100
Brand	-
UBB	952351624509
UNSPSC	31161518
EAN	8715492265241
PKG. of 50	Full Box Only

**Technical Parameters**

Diameter	M8
Length	100 mm
Driving features	Hexagon socket
Head shape	Countersunk head
Material	Stainless steel
Material technical	A2
Thread direction	Right
Thread	Metric thread

Info	All thread lengths are guide values only and may deviate. Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class
------	--

**Standards**

ISO	10642
-----	-------

mark, e.g. 'A2-070',  
or with the steel  
grade only, e.g. 'A2'.

## Technical Specification

b (min.)	28
d-D	M8
dk (max.)	16.43
Full thread if $L \leq$	45
k (max.)	4.96
L (mm)	100
P	1.25
s	5
$\alpha$	90

## Technical Drawing

