



## Hexagon socket countersunk head screw ISO 10642 Stainless steel A2 M20X130

Article number	51060.200.130
Brand	-
UBB	500571274124
UNSPSC	31161518
EAN	8715494132220
PKG. of 25	Full Box Only

### Technical Parameters

Diameter	M20
Length	130 mm
Driving features	Hexagon socket
Head shape	Countersunk head
Material	Stainless steel
Material technical	A2
Thread direction	Right
Thread	Metric thread

Info	All thread lengths are guide values only and may deviate. Due to the unfavourable head geometry these fasteners have reduced loadability. Steel fasteners with reduced loadability are marked with a '0' preceding the property class mark, e.g. '010.9'. Stainless steel fasteners with reduced loadability are either marked with a '0' preceding the property class
------	--

### Standards

ISO	10642
-----	-------

mark, e.g. 'A2-070',  
or with the steel  
grade only, e.g. 'A2'.

## Technical Specification

b (min.)	60
d-D	M20
dk (max.)	36.75
Full thread if $L \leq$	90
k (max.)	10.16
L (mm)	130
P	2.5
s	12
$\alpha$	90

## Technical Drawing

