

Threaded rod length 1 meter DIN 976-1A Stainless steel A2 Min.50 M30



Article number	51070.300.001
Brand	-
UBB	950353243674
UNSPSC	31161618
EAN	8715492266903
PKG. of 1	Full Box Only

Technical Parameters

Length (L) (mm)	1000
Diameter (d-D)	M30
Class	Min.50
Extra info	1 meter
Material	Stainless steel
Material technical	A2
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M3 or M24 are minimal property class 50.

Standards

NF	E25-136
DIN	976-1A

Technical Specification

P	3.50
---	------

Technical Drawing

