



Threaded rod DIN 976-1A Stainless Steel A2 1 mtr Min.50 M33

Article number	51070.330.001
Brand	-
UBB	950353243757
UNSPSC	31161618
EAN	8715492266910
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M33
Length	1000 mm
Class	Min.50
Material	Stainless steel
Material technical	A2
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M3 or M24 are minimal property class 50.1 meter

Standards

NF	E25-136
DIN	976-1A

Technical Specification

d-D	M33
L (mm)	1000
P	3.5

Technical Drawing

