



Threaded rod DIN 976-1A Stainless Steel A2 2 mtr Min.50 M45

Article number	51071.450.001
Brand	-
UBB	500633175939
UNSPSC	31161618
EAN	8715494611800
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M45
Length	2000 mm
Class	Min.50
Material	Stainless steel
Material technical	A2
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M3 or M24 are minimal property class 50.2 meter

Standards

NF	E25-136
DIN	976-1A

Technical Specification

d-D	M45
L (mm)	2000
P	4.5

Technical Drawing

