



Threaded rod length 3 meter
DIN 976-1A Stainless steel
A2 70 M12

Article number	51072.120.001
Brand	-
UBB	950353543644
UNSPSC	31161618
EAN	8715492267047
PKG. of 2	Full Box Only

Technical Parameters

Diameter	M12
Length	3000 mm
Class	70
Material	Stainless steel
Material technical	A2
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M3 or M24 are minimal property class 50.3 meter

Standards

DIN	976-1A
NF	E25-136

Technical Specification

d-D	M12
L (mm)	3000
P	1.75

Technical Drawing

