



Threaded rod length 3 meter
DIN 976-1A Stainless steel
A2 70 M18

Article number	51072.180.001
Brand	-
UBB	500633176192
UNSPSC	31161618
EAN	8715494611824
PKG. of 5	Full Box Only

Technical Parameters

Diameter	M18
Length	3000 mm
Class	70
Material	Stainless steel
Material technical	A2
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M3 or M24 are minimal property class 50.3 meter

Standards

NF	E25-136
DIN	976-1A

Technical Specification

d-D	M18
L (mm)	3000
P	2.5

Technical Drawing

