



Hexagon nut DIN 934 Stainless steel A2 70 M5

Article No.	51080.050.001
Brand	-
UBB	950355217643
UNSPSC	31161727
EAN	8715492267351
PKG. of 500	Full Box Only

Technical Parameters

Diameter (d-D)	M5
Class	70
Driving features	Hexagon
Material	Stainless steel
Material technical	A2
Thread direction	Right
Thread	Metric thread
Info	Sizes with a diameter M39 are minimal property class 50.

Standards

DIN	934
NF	E25-401
NEN	1560

Technical Specification

m	4
P	0.80
s	8

Technical Drawing

