

## Hexagon nut DIN 934 Stainless steel A2 Zinc plated 70 M8

|                |               |
|----------------|---------------|
| Article number | 51085.080.001 |
| Brand          | -             |
| UBB            | 500627337099  |
| UNSPSC         | 31162400      |
| EAN            | 8715494538244 |
| PKG. of 200    | Full Box Only |

### Technical Parameters

|                    |                                                                                                                                   |
|--------------------|-----------------------------------------------------------------------------------------------------------------------------------|
| Diameter           | M8                                                                                                                                |
| Class              | 70                                                                                                                                |
| Driving features   | Hexagon                                                                                                                           |
| Material           | Stainless steel                                                                                                                   |
| Material technical | A2                                                                                                                                |
| Thread direction   | Right                                                                                                                             |
| Surface treatment  | Zinc plated                                                                                                                       |
| Thread             | Metric thread                                                                                                                     |
| Info               | The thin zinc layer on stainless steel nuts reduces the risk of galling. Sizes with a diameter M20 are minimal property class 50. |

### Standards

|     |         |
|-----|---------|
| DIN | 934     |
| NF  | E25-401 |
| NEN | 1560    |

### Technical Specification

|     |      |
|-----|------|
| d-D | M8   |
| m   | 6.5  |
| P   | 1.25 |
| s   | 13   |

### Technical Drawing

