

Hexagon nut DIN 934 Stainless steel A2 Zinc plated Min.50 M24

Article number	51085.240.001
Brand	-
UBB	500627337586
UNSPSC	31162400
EAN	8715494538299
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M24
Class	Min.50
Driving features	Hexagon
Material	Stainless steel
Material technical	A2
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread
Info	The thin zinc layer on stainless steel nuts reduces the risk of galling.Sizes with a diameter M20 are minimal property class 50.

Standards

NEN	1560
DIN	934
NF	E25-401

Technical Specification

d-D	M24
m	19
P	3
s	36

Technical Drawing

