

## Hexagon nut DIN 934 Stainless steel A2 METALFORM 70 M5

Article number	51089.050.001
Brand	-
UBB	950355975661
UNSPSC	31161727
EAN	8715492267863
PKG. of 250	Full Box Only

### Technical Parameters

Diameter	M5
Class	70
Driving features	Hexagon
Material	Stainless steel
Material technical	A2
Thread direction	Right
Surface treatment	METALFORM
Thread	Metric thread

Info	Sizes with a diameter M20 are minimal property class 50. Specific features of Metalform: The fixed, slightly visible dry film lubricant reduces the effect of galling. It levels out the big scatter in coefficient of friction and reduces the average value. In a bolt/nut assembly only one product (e.g. the nut) needs to be lubricated with Metalform. The lubricant can easily be removed with
------	---

### Standards

DIN	934
NF	E25-401
NEN	1560

a solvent after assembly, there's no objection against application in the food industry.

## Technical Specification

d-D	M5
m	4
P	0.8
s	8

## Technical Drawing

