



## Hexagon nut DIN 934 Stainless steel A2 METALFORM 70 M6

Article number	51089.060.001
Brand	-
UBB	950355975745
UNSPSC	31161727
EAN	8715492267870
PKG. of 250	Full Box Only

### Technical Parameters

Diameter (d-D)	M6
Class	70
Driving features	Hexagon
Material	Stainless steel
Material technical	A2
Thread direction	Right
Surface treatment	METALFORM
Thread	Metric thread

### Standards

DIN	934
NF	E25-401

**Info**

Sizes with a diameter M20 are minimal property class 50. Specific features of Metalform: The fixed, slightly visible dry film lubricant reduces the effect of galling. It levels out the big scatter in coefficient of friction and reduces the average value. In a bolt/nut assembly only one product (e.g. the nut) needs to be lubricated with Metalform. The lubricant can

easily be removed with a solvent after assembly, there's no objection against application in the food industry.

### Technical Specification

m	5
P	1
s	10

### Technical Drawing

