

Hexagon nut DIN 934 Stainless steel A2 METALFORM 70 M10

Article number	51089.100.001
Brand	-
UBB	950355975901
UNSPSC	31161727
EAN	8715492267894
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M10
Class	70
Driving features	Hexagon
Material	Stainless steel
Material technical	A2
Thread direction	Right
Surface treatment	METALFORM
Thread	Metric thread

Standards

DIN	934
NF	E25-401
NEN	1560

Info

Sizes with a diameter M20 are minimal property class 50. Specific features of Metalform: The fixed, slightly visible dry film lubricant reduces the effect of galling. It levels out the big scatter in coefficient of friction and reduces the average value. In a bolt/nut assembly only one product (e.g. the nut) needs to be lubricated with Metalform. The lubricant can easily be removed with

a solvent after assembly, there's no objection against application in the food industry.

Technical Specification

d-D	M10
m	8
P	1.5
s	17

Technical Drawing

