

## Hexagon nut DIN 934 Stainless steel A2 METALFORM 70 M16

Article number	51089.160.001
Brand	-
UBB	950355976164
UNSPSC	31161727
EAN	8715492267917
PKG. of 50	Full Box Only

### Technical Parameters

Diameter	M16
Class	70
Driving features	Hexagon
Material	Stainless steel
Material technical	A2
Thread direction	Right
Surface treatment	METALFORM
Thread	Metric thread

### Standards

NF	E25-401
DIN	934
NEN	1560

**Info**

Sizes with a diameter M20 are minimal property class 50. Specific features of Metalform: The fixed, slightly visible dry film lubricant reduces the effect of galling. It levels out the big scatter in coefficient of friction and reduces the average value. In a bolt/nut assembly only one product (e.g. the nut) needs to be lubricated with Metalform. The lubricant can easily be removed with

a solvent after assembly, there's no objection against application in the food industry.

### Technical Specification

d-D	M16
m	13
P	2
s	24

### Technical Drawing

