



Hexagon nut with flange DIN 6923 Stainless steel A2 70 M10

Article number	51108.100.001
Brand	-
UBB	950355814878
UNSPSC	31161727
EAN	8715492268891
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M10
Class	70
Driving features	Hexagon
Material	Stainless steel
Material technical	A2
Thread direction	Right
Thread	Metric thread

Info	Specific features of hexagon nuts with flange:The flange enables built up forces under the nut to be spread over a larger area, consequently resulting in lower surface pressure.Large (oversized) holes and/or tooling holes can be covered by the flange.Washers are not necessary.
------	---

Standards

ISO	4161
DIN	6923
NF	E25-406

Technical Specification

d-D	M10
-----	-----

Technical Drawing

dc (max.) 21.8

m (max.) 10

P 1.5

s 15

