



Slotted countersunk head screw DIN 963 A Stainless steel A2 large pack M1X10

Article number	51110.010.010
Brand	-
UBB	500633178743
UNSPSC	31161504
EAN	8715494612081
PKG. of 1000	Full Box Only

Technical Parameters

Diameter	M1
Length	10 mm
Class	70
Driving features	Slotted
Head shape	Countersunk head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

BS	≈4183
NEN	≈2370
ISO	≈2009
NF	≈E25-123
DIN	963
ASME	≈B18.6.7M

Technical Specification

d-D	M1
Thread length (min.)	5
dk (max.)	1.9
Full thread if $L \leq$	5
k (max.)	0.6
L (mm)	10
n	0.25
P	0.25
t (min.)	0.2

Technical Drawing

