



Slotted countersunk head screw DIN 963 A Stainless steel A2 large pack M1,2X2

Article number	51110.012.002
Brand	-
UBB	500633178826
UNSPSC	31161504
EAN	8715494612098
PKG. of 1000	Full Box Only

Technical Parameters

Diameter	M1.2
Length	2 mm
Class	70
Driving features	Slotted
Head shape	Countersunk head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

BS	≈4183
NF	≈E25-123
NEN	≈2370
ASME	≈B18.6.7M
ISO	≈2009
DIN	963

Technical Specification

d-D	M1.2
Thread length (min.)	5
dk (max.)	2.3
Full thread if $L \leq$	5
k (max.)	0.72
L (mm)	2
n	0.3
P	0.25
t (min.)	0.25

Technical Drawing

