



Slotted countersunk head screw DIN 963 Stainless steel A2 70 M2X5

Article number	51110.020.005
Brand	-
UBB	950353245240
UNSPSC	31161504
EAN	8715492268990
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M2
Length	5 mm
Class	70
Driving features	Slotted
Head shape	Countersunk head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

ASME	≈B18.6.7M
ISO	≈2009
DIN	963
NF	≈E25-123
BS	≈4183
NEN	≈2370

Technical Specification

d-D	M2
Thread length (min.)	16
dk (max.)	3.8
Full thread if $L \leq$	18
k (max.)	1.2
L (mm)	5
n	0.5
P	0.4
t (min.)	0.4

Technical Drawing

