



Slotted countersunk head screw DIN 963 Stainless steel A2 70 M2X16

Article number	51110.020.016
Brand	-
UBB	950353245737
UNSPSC	31161504
EAN	8715492269041
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M2
Length	16 mm
Class	70
Driving features	Slotted
Head shape	Countersunk head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

DIN	963
BS	≈4183
NF	≈E25-123
ISO	≈2009
ASME	≈B18.6.7M
NEN	≈2370

Technical Specification

d-D	M2
Thread length (min.)	16
dk (max.)	3.8
Full thread if $L \leq$	18
k (max.)	1.2
L (mm)	16
n	0.5
P	0.4
t (min.)	0.4

Technical Drawing

