



## Hexagon nut with serrated flange DIN ≈6923 Stainless steel A2 M3

Article number	51119.030.001
Brand	-
UBB	500571679058
UNSPSC	31161727
EAN	8715494103701
PKG. of 500	Full Box Only

### Technical Parameters

Diameter	M3
Driving features	Hexagon
Material	Stainless steel
Material technical	A2
Thread direction	Right
Thread	Metric thread

### Standards

DIN	≈6923
ISO	≈4161
NF	≈E25-406

**Info**

Specific features of hexagon nuts with serrated flange: The flange enables built up forces under the nut to be spread over a larger area, consequently resulting in lower surface pressure. Large (oversized) holes and/or tooling holes can be covered by the flange. Washers are not necessary. The serrated flange provides an excellent self-locking effect.

### Technical Specification

d-D	M3
-----	----

### Technical Drawing

dc (max.)	7.8
m (max.)	3.8
P	0.5
s	6

