



Hexagon nut with serrated flange DIN ≈6923 Stainless steel A2 M10

Article number	51119.100.001
Brand	-
UBB	500571679546
UNSPSC	31161727
EAN	8715494103756
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M10
Driving features	Hexagon
Material	Stainless steel
Material technical	A2
Thread direction	Right
Thread	Metric thread

Info	Specific features of hexagon nuts with serrated flange:The flange enables built up forces under the nut to be spread over a larger area, consequently resulting in lower surface pressure.Large (oversized) holes and/or tooling holes can be covered by the flange.Washers are not necessary.The serrated flange provides an excellent self-locking effect.
------	--

Standards

DIN	≈6923
NF	≈E25-406
ISO	≈4161

Technical Specification

d-D	M10
-----	-----

Technical Drawing

dc (max.) 21.8

m (max.) 10

P 1.5

s 15

