



Slotted cheese head screw DIN 84 Stainless steel A2 70 M1,2X3

Article number	51120.012.003
Brand	-
UBB	950353255132
UNSPSC	31161504
EAN	8715492270603
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M1.2
Length	3 mm
Class	70
Driving features	Slotted
Head shape	Cylindrical head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

DIN	84
NF	≈E25-127
BS	≈4183
NEN	≈1602
ASME	≈B18.6.7M
ISO	≈1207

Technical Specification

d-D	M1.2
Thread length (min.)	25
dk (max.)	2.3
Full thread if L ≤	30
k (max.)	0.8
L (mm)	3
n	0.3
P	0.25
t (min.)	0.3

Technical Drawing