



Slotted cheese head screw DIN 84 Stainless steel A2 70 M1,6X12

Article number	51120.016.012
Brand	-
UBB	950353256387
UNSPSC	31161504
EAN	8715492270740
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M1.6
Length	12 mm
Class	70
Driving features	Slotted
Head shape	Cylindrical head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

BS	≈4183
DIN	84
NEN	≈1602
NF	≈E25-127
ASME	≈B18.6.7M
ISO	≈1207

Technical Specification

d-D	M1.6
Thread length (min.)	25
dk (max.)	3
Full thread if L ≤	30
k (max.)	1
L (mm)	12
n	0.4
P	0.35
t (min.)	0.45

Technical Drawing