



Slotted cheese head screw DIN 84 Stainless steel A2 70 M2X4

Article number	51120.020.004
Brand	-
UBB	950353455781
UNSPSC	31161504
EAN	8715492270764
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M2
Length	4 mm
Class	70
Driving features	Slotted
Head shape	Cylindrical head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

ISO	≈1207
BS	≈4183
ASME	≈B18.6.7M
NEN	≈1602
NF	≈E25-127
DIN	84

Technical Specification

d-D	M2
Thread length (min.)	25
dk (max.)	3.8
Full thread if L ≤	30
k (max.)	1.3
L (mm)	4
n	0.5
P	0.4
t (min.)	0.5

Technical Drawing