



Slotted cheese head screw DIN 84 Stainless steel A2 70 M2X30

Article number	51120.020.030
Brand	-
UBB	500633418099
UNSPSC	31161504
EAN	8715494600767
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M2
Length	30 mm
Class	70
Driving features	Slotted
Head shape	Cylindrical head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

BS	≈4183
ASME	≈B18.6.7M
NEN	≈1602
DIN	84
NF	≈E25-127
ISO	≈1207

Technical Specification

d-D	M2
Thread length (min.)	25
dk (max.)	3.8
Full thread if L ≤	30
k (max.)	1.3
L (mm)	30
n	0.5
P	0.4
t (min.)	0.5

Technical Drawing