



## Slotted cheese head screw DIN 84 Stainless steel A2 70 M2,3X4

|                |               |
|----------------|---------------|
| Article number | 51120.023.004 |
| Brand          | -             |
| UBB            | 500633418255  |
| UNSPSC         | 31161504      |
| EAN            | 8715494600781 |
| PKG. of 1000   | Full Box Only |

### Technical Parameters

|                    |                  |
|--------------------|------------------|
| Diameter           | M2.3             |
| Length             | 4 mm             |
| Class              | 70               |
| Driving features   | Slotted          |
| Head shape         | Cylindrical head |
| Material           | Stainless steel  |
| Material technical | A2               |
| Thread             | Metric thread    |

### Standards

|      |           |
|------|-----------|
| BS   | ≈4183     |
| NEN  | ≈1602     |
| ISO  | ≈1207     |
| NF   | ≈E25-127  |
| DIN  | 84        |
| ASME | ≈B18.6.7M |

### Technical Specification

|                      |      |
|----------------------|------|
| d-D                  | M2.3 |
| Thread length (min.) | 25   |
| dk (max.)            | 4.4  |
| Full thread if L ≤   | 30   |
| k (max.)             | 1.5  |
| L (mm)               | 4    |
| n                    | 0.6  |
| P                    | 0.45 |
| t (min.)             | 0.6  |

### Technical Drawing