



Hexalobular socket head cap screw ISO 14580 Stainless steel A2 50 M3X6

Article number	51122.030.006
Brand	-
UBB	500571832178
UNSPSC	31161501
EAN	8715494113021
PKG. of 1000	Full Box Only

Technical Parameters

Diameter	M3
Length	6 mm
Class	50
Driving features	Hexalobular
Head shape	Low cylindrical head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

ISO	14580
-----	-------

Technical Specification

b (min.)	25
d-D	M3
dk (max.)	5.5
k (max.)	2.4
L (mm)	6
P	0.5
Socket	10

Technical Drawing

