



Slotted pan head screw DIN 85 Stainless steel A2 70 M1,6X5

Article number	51140.016.005
Brand	-
UBB	500633184352
UNSPSC	31161504
EAN	8715494612661
PKG. of 1000	Full Box Only

Technical Parameters

Diameter	M1.6
Length	5 mm
Class	70
Driving features	Slotted
Head shape	Pan head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

DIN	85
NF	≈E25-128
ASME	≈B18.6.7M
NEN	≈1603
BS	≈4183
ISO	≈1580

Technical Specification

d-D	M1.6
Thread length (min.)	25
dk (max.)	3.2
Full thread if $L \leq$	16
k (max.)	1
L (mm)	5
n	0.5
P	0.35
t (min.)	0.35

Technical Drawing

