



Slotted pan head screw DIN 85 Stainless steel A2 70 M2X4

Article number	51140.020.004
Brand	-
UBB	500633184683
UNSPSC	31161504
EAN	8715494612692
PKG. of 1000	Full Box Only

Technical Parameters

Diameter	M2
Length	4 mm
Class	70
Driving features	Slotted
Head shape	Pan head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

NF	≈E25-128
BS	≈4183
DIN	85
ISO	≈1580
NEN	≈1603
ASME	≈B18.6.7M

Technical Specification

d-D	M2
Thread length (min.)	25
dk (max.)	4
Full thread if $L \leq$	16
k (max.)	1.3
L (mm)	4
n	0.5
P	0.4
t (min.)	0.5

Technical Drawing

