

Slotted pan head screw DIN 85 Stainless steel A2 70 M2X8



Article number 51140.020.008

Brand -

UBB 500633184840

UNSPSC 31161504

EAN 8715494612715

PKG. of 1000 Full Box Only

Technical Parameters

Diameter (d-D)	M2
Length (L) (mm)	8
Class	70
Driving features	Slotted
Head shape	Pan head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

ISO	≈1580
BS	≈4183
DIN	85
ASME	≈B18.6.7M
NF	≈E25-128

Technical Specification

Thread length (min.)	25
d_k (max.)	4
Full thread if $L \leq$	16
k (max.)	1.3
n	0.5
P	0.40
t (min.)	0.5

Technical Drawing

