



Slotted pan head screw DIN 85 Stainless steel A2 70 M2X12

Article number	51140.020.012
Brand	-
UBB	500571397719
UNSPSC	31161504
EAN	8715494126168
PKG. of 1000	Full Box Only

Technical Parameters

Diameter	M2
Length	12 mm
Class	70
Driving features	Slotted
Head shape	Pan head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

BS	≈4183
ISO	≈1580
NEN	≈1603
NF	≈E25-128
DIN	85
ASME	≈B18.6.7M

Technical Specification

d-D	M2
Thread length (min.)	25
dk (max.)	4
Full thread if $L \leq$	16
k (max.)	1.3
L (mm)	12
n	0.5
P	0.4
t (min.)	0.5

Technical Drawing

