



## Slotted pan head screw DIN 85 Stainless steel A2 70 M2,5X4

|                |               |
|----------------|---------------|
| Article number | 51140.025.004 |
| Brand          | -             |
| UBB            | 500633185268  |
| UNSPSC         | 31161504      |
| EAN            | 8715494612753 |
| PKG. of 1000   | Full Box Only |

### Technical Parameters

|                    |                 |
|--------------------|-----------------|
| Diameter           | M2.5            |
| Length             | 4 mm            |
| Class              | 70              |
| Driving features   | Slotted         |
| Head shape         | Pan head        |
| Material           | Stainless steel |
| Material technical | A2              |
| Thread             | Metric thread   |

### Standards

|      |           |
|------|-----------|
| DIN  | 85        |
| BS   | ≈4183     |
| ISO  | ≈1580     |
| NEN  | ≈1603     |
| NF   | ≈E25-128  |
| ASME | ≈B18.6.7M |

### Technical Specification

|                         |      |
|-------------------------|------|
| d-D                     | M2.5 |
| Thread length (min.)    | 25   |
| dk (max.)               | 5    |
| Full thread if $L \leq$ | 16   |
| k (max.)                | 1.5  |
| L (mm)                  | 4    |
| n                       | 0.6  |
| P                       | 0.45 |
| t (min.)                | 0.6  |

### Technical Drawing

