



Slotted pan head screw DIN 85 Stainless steel A2 70 M8X35

Article number	51140.080.035
Brand	-
UBB	950353466267
UNSPSC	31161504
EAN	8715492273604
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M8
Length	35 mm
Class	70
Driving features	Slotted
Head shape	Pan head
Material	Stainless steel
Material technical	A2
Thread	Metric thread

Standards

NF	≈E25-128
NEN	≈1603
ISO	≈1580
ASME	≈B18.6.7M
DIN	85
BS	≈4183

Technical Specification

d-D	M8
Thread length (min.)	38
dk (max.)	16
Full thread if $L \leq$	40
k (max.)	4.8
L (mm)	35
n	2
P	1.25
t (min.)	1.9

Technical Drawing

